

Planetary Centrifugal Mixer **THINKY MIXER ARM-310** (\in

Reproducibility, Homogeneity, Effectivity by 400G

- Mixing a wide range of materials from low to high viscosity
- Shortening the time for mixing and improving overall working process
- Compatible with 3 ml 300 ml syringe/container
- 70 standard container, 30 standard adapters
- Custom-made adapters available fits your container







Specifications

Product Name	Planetary centrifugal mixer "THINKY MIXER"
Model	ARM-310 CE
System	Planetary, propeller-less mixing
Operation Time Setting	Timer setting range: 0 s to 30 min in 1 s increments
Programming Function	STD mode: 5 memories with 1 step STEP mode: 5 memories with 5 steps
Revolution speed (rpm)	STD mode (2000 rpm fixed) STEP mode (0, 200-2000 rpm)
Rotation Speed (rpm)	Max. 800 rpm

Maximum Capacity		310g
Standard Container		300 ml resin container
Power Supply	Voltage	Single-phase AC230 V \pm 10%, 50 Hz
	Power Consumption	Approx. 50 VA (standby) Max 900 VA (operation)
Operating Environment		10 to 35 °C, 35 to 85 % RH (without condensation)
Unit Dimensions		H390 × W300 × D340 (mm)
Unit Weight		Approx. 21 kg

Product appearance/specifications may change without notice.

Sales agent

THINKY CORPORATION

Headquarters: 2-16-2 Sotokanda, Chiyoda-ku, Tokyo 101-0021 Phone : +81-3-5207-2713 Fax : +81-3-5289-3281 THINKY USA Inc. : 23151 Verdugo Drive, Suite 112 Laguna Hills, CA92653, USA THINKY CHINA: East building, HaiAn Kafunuo Mansion, Shennan road, Qianhai road, Nanshan district, Shenzhen

http://www.thinkymixer.net/ Email: info@thinkymixer.net